

## บริษัท สลิงอ่อน (ประเทศไทย) จำกัด SOFT-SLING (THAILAND) LIMITED

40/6-7 RAMKHUMHAENG RD., HUAMARK, BANGKAPI, BANGKOK 10240

TEL: (02) 3793840, 7316000-2 FAX: (02) 3793889

www.softsling.co.th , email : soft1@softsling.co.th,soft2@softsling.co.th

## DRUM HANDLING SLINGS







WIDTH	STOCK NUMBER	ASSEMBLY CAPACITY
2 IN	DS1-602	750 K <i>G</i> S.
2 IN	DS1-602 ADJ*	750 K <i>G</i> S.

DRUM HANDLING ARE SPECIFICALLY DESIGNED FOR THE EFFICIENT HANDLING OF 55 GALLON, RIBBED, METAL DRUMS. IT CAN BE USED TO LIFT OPEN TOP DRUMS, OR EVEN DRUMS FITTED WITH SPIGOTS OR PUMPS.

THE SLING CONSISTS OF A 2-INCH LIFT LOOP AND A 2-INCH CIRCUMFERENTIAL TIGHTENING BAND. THE LIFT LOOP IS PERMANENTLY ATTACHED TO THE TIGHTENING BAND, THUS ELIMINATING THE NEED TO POSITION THE LOOP FOR LIFTING.

BOTH THE LIFTING LOOP AND THE TIGHTENING BAND ARE LINED WITH A FULL LENGTH LEATHER WEAR PAD FOR WEAR PROTECTION.

THE TIGHTENING BAND SECURELY GRIPS THE DRUM BELOW THE FIRST RIB. WHEN MAKING THE LIFT, KEEP THE LOAD LOW, LIFTING THE DRUM ONLY ENOUGH TO CLEAR THE GROUND.

\* SPECIFY THE **DS1-602ADJ**, ADJUSTABLE DRUM SLING WHEN DRUMS WITH VARYING DIAMETERS ARE TO BE HANDLED. THIS MODEL IS THE SAME AS THE STANDARD **DS1-602** MODEL, EXCEPT ONLY ONE OF THE LIFT LOOP LEGS IS ATTACHED TO THE CIRCUMFERENTIAL TIGHTENING BAND. THE UNATTACHED LEG IS FREE TO BE POSITIONED FOR VARIOUS DRUM DIAMETERS. THE LEATHER WEAR PAD NORMALLY ATTACHED TO THE TIGHTENING BAND IS OMITTED ON THE ADJUSTABLE MODEL TO FACILITATE EASY USE.

DO NOT EXCEED RATED CAPACITY.